





Type T1
Id. no. 1

Type T0
Id. no. 2


Type T2
Id. no. 2



Plug M12x1, 12-pole



Door opening left L



Door opening right R

3 Type

- T0 Without button
- T1 With 1 button
- T2 With 2 buttons

4 Identification no.

- 1 Without emergency stop
- 2 With emergency stop

5 Door opening

- L Left
- R Right

Length l ±0,25	d	b ₁	b ₂	b ₃	b ₄	h ₁	h ₂	t min.
200	M 8	27	17	51	68	51	68	15
300	M 8	27	17	51	68	51	68	15

Specification

Handle tube

- Aluminum, wall thickness 1,5 mm
- Powder coated
- Black, RAL 9005, textured finish
- Anodized, natural color

- SW
- EL

Handle legs

- Zinc die casting
- Powder coated
- Black, RAL 9005, textured finish

Cover for identification no. 1

- (instead of emergency stop)
- Plastic, light gray

Operating temperature -25 °C to +55 °C

RoHS

Tubular handles GN 332 are available with various options for emergency stops and buttons. They can be used for activating individual functions of a machine control, such as unlocking the safety lock of a housing door right on the handle.

The possible switching operations depend on the options and are described below. For types T1 and T2, one set of caps (consisting of the colors red, green, and blue) is supplied for each button.

The red or green LED lights up regardless of whether the button is pressed and can be used to indicate the status of a control, for example.

see also...

	Page
GN 331 Tubular Handles (Straight, with Electrical Switching Function)	QVX
GN 333 Tubular Handles (Angled, without Electrical Switching Function)	QVX
GN 422 Cabinet U-Handles (Zinc Die Casting, with Electrical Switching Function)	QVX
GN 628.4 Cabinet U-Handles (Plastic, with Electrical Switching Function)	QVX

Technical Information

Characteristics of the standard executions	QVX
Load Rating Information	QVX
IP Protection Classes	QVX

Accessory










GN 330 Cables with Connector Coupling (12-pole, 5 or 10 meters long)	QVX
--	-----

How to order

1	Length l
2	Finish
3	Type
4	Identification no.
5	Door opening

GN 332-200-SW-T1-2-L



Characteristics of the standard executions GN 332		
The tubular handles have the CE marking, low voltage guideline 2014 / 35 / EU		
Emergency stop	2 channel, normally closed contact	
1st button with 2 LED	Changeover contact	
	LED, red and green	
2nd button	Normally open contact	
Contact termination, Pin configuration	Plug M12x1, 12-pole	
Switching voltage / Switching current	max. 24 V DC / max. 0,5 A	
Operating voltage (LEDs)	24 V DC ±15% / 10 mA	
Protection class	Identification no. 1: IP 67 (in screwed condition) Identification no. 2: IP 54	
Button color	for each button a set of caps is included, in this colors: red, green, blue	
Additional variations as special application		
Emergency stop	1 channel	
Number of buttons > 2 Button optional with	Normally open contact	
	Normally closed contact	
	Changeover contact	
Button with labelling area	