



#### 4 Type (Base)

- A1** Steel, zinc plated rubber inlaid, black
- A2** Steel, zinc plated rubber inlaid, white
- A5** Steel, plastic coated, black rubber inlaid, black

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>								l <sub>7</sub> Vers. X	h <sub>1</sub>	h <sub>2</sub>	s		
		Version S / SK				Version U / UK									
50	M 8	40	50	63	-	-	-	-	-	-	37	14,5	3,5	3	
50	M 10	50	60	80	100	-	-	-	-	-	40	14,5	3,5	3	
50	M 12	60	80	100	125	-	-	-	-	-	43	14,5	3,5	3	
50	M 16	-	-	-	-	75	100	125	150	200	250	49	14,5	3,5	3
60	M 8	40	50	63	-	-	-	-	-	-	38	16	4	3	
60	M 10	50	60	80	100	-	-	-	-	-	41	16	4	3	
60	M 12	60	80	100	125	-	-	-	-	-	45	16	4	3	
60	M 16	-	-	-	-	75	100	125	150	200	250	50	16	4	3
80	M 8	40	50	63	-	-	-	-	-	-	40	18	5	3	
80	M 10	50	60	80	100	-	-	-	-	-	43	18	5	3	
80	M 12	60	80	100	125	-	-	-	-	-	47	18	5	3	
80	M 16	-	-	-	-	75	100	125	150	200	250	52	18	5	3
80	M 20	-	-	-	-	75	100	125	150	200	250	60	18	5	3
80	M 24	-	-	-	-	100	125	150	200	300	-	18	5	3	
100	M 8	40	50	63	-	-	-	-	-	-	42	20	6	3	
100	M 10	50	60	80	100	-	-	-	-	-	45	20	6	3	
100	M 12	60	80	100	125	-	-	-	-	-	49	20	6	3	
100	M 16	-	-	-	-	75	100	125	150	200	250	54	20	6	3
100	M 20	-	-	-	-	75	100	125	150	200	250	62	20	6	3
100	M 24	-	-	-	-	100	125	150	200	300	-	20	6	3	
120	M 20	-	-	-	-	100	125	150	200	250	-	65	22	6	4
120	M 24	-	-	-	-	100	125	150	200	300	-	22	6	4	
120	M 30	-	-	-	-	100	125	150	200	300	-	22	6	4	

## Specification

- Base plate, steel sheet metal
  - Type A1, A2: Steel, zinc plated, blue passivated
  - Type A5: Steel, powder coated Black, RAL 9005
- Threaded stem
  - Steel, zinc plated, blue passivated
- Hex nut ISO 4032
  - Steel, zinc plated, blue passivated
- Rubber pad, inlaid
  - Black: NBR (Perbunan®) 80±5 Shore A
  - White: TPE (Santoprene®) 80±5 Shore A

• RoHS

**Versions of threaded stem**

<p><b>S</b> Without nut <b>SK</b> With nut</p>	<p><b>U</b> Without nut <b>UK</b> With nut</p>	<p><b>X</b> With internal thread</p>
<p>External hex at the bottom at <math>d_2</math> M 8, M 10, M 12</p>	<p>Hex socket at the top and wrench flat at the bottom at <math>d_2</math> M 16, M 20, M 24, M 30</p>	<p>External hex with internal thread at <math>d_2</math> M 8, M 10, M 12, M 16, M 20</p>

$d_1$	$d_2$	$h_3$	$h_4$	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>7</sub>	t
50	M 8	23	-	17	-	-	14	8
50	M 10	23	-	17	-	-	14	10
50	M 12	23	-	17	-	-	17	12
50	M 16	-	29	-	12	8	22	16
60	M 8	24	-	17	-	-	14	8
60	M 10	24	-	17	-	-	14	10
60	M 12	24	-	17	-	-	17	12
60	M 16	-	30	-	12	8	22	16
80	M 8	26	-	17	-	-	14	8
80	M 10	26	-	17	-	-	14	10
80	M 12	26	-	17	-	-	17	12
80	M 16	-	32	-	12	8	22	16
80	M 20	-	33	-	15	10	27	20
80	M 24	-	36	-	19	12	-	-
100	M 8	28	-	17	-	-	14	8
100	M 10	28	-	17	-	-	14	10
100	M 12	28	-	17	-	-	17	12
100	M 16	-	34	-	12	8	22	16
100	M 20	-	35	-	15	10	27	20
100	M 24	-	38	-	19	12	-	-
120	M 20	-	39	-	15	10	27	20
120	M 24	-	42	-	19	12	-	-
120	M 30	-	46	-	24	12	-	-

**Information**

Leveling feet GN 30 will be delivered mounted and are not removable.

- [Load Rating Information](#) → Page 2142
- [Elastomer Characteristics](#) → Page 2158

see also...

- [Leveling Feet GN 32 \(Steel, with Mounting Flange\)](#) → Page 1480
- [Stainless Steel Leveling Feet GN 31](#) → Page 1478
- [Insert Bushings GN 448 \(for Tubes\)](#) → Page 1498 / 1499

**How to order**

1	$d_1$
2	$d_2$
3	$l_1$ ( $l_7$ )
4	Type (Base plate)
5	Version (Stem)

GN 30-120-M30-125-A1-UK