



Installation holes



Application examples



d ₁ For rod / tube	h ₁	b	d ₂	d ₃	d ₄	d ₅	d ₆	h ₂	m	sw	t min.
30 +0,1 / -0,25	60	27,5	M 10	46	46,6	42	8	84	13,5	5	20
40 +1 0,5 / -0,3	70	30	M 12	56	56,8	50	8	99	18,5	5	25

Specification

Handle leg

Stainless steel AISI 304

NI

Ground, matte finish (Ra < 0.8 µm)

MT

Sealing ring / wiper

TPU

T

• Operating temperature -20 °C to +110 °C

• FDA compliant material

• Blue

• Hardness 95 ±5 Shore A

Clamping wedge

Brass

Grub screw

Stainless steel

RoHS

Accessory

Page

GN 1580 Screws

QVX

GN 1581 Screws

QVX

Handle legs GN 3331 comply with the DGUV testing principles and are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the non-concave geometry prevent adherence of dirt and facilitate cleaning.

The handle legs are designed for use with tubular handles GN 3330 to reduce large distances between mounting points or excessive loads on the handle legs. Regardless of the handle application, supports can be used to fix rods and tubes with the corresponding diameter d₁. The tube or rod is fastened during installation using the integrated clamping wedge.

see also...

GN 3330 Tubular Handles (Stainless steel, Hygienic Design)

Page

QVX

Technical Information

Product Family Hygienic Design

QVX

Plastic Characteristics

QVX

Stainless Steel Characteristics

QVX

How to order

1	Material
2	d ₁
3	h ₁
4	Finish
5	Material (seals)

GN 3331-NI-40-70-MT-T

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4