




1	2	3									d ₃	d ₄	h ₁	h ₂	h ₃	h ₄
l ₁	d ₁		l ₂								d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
22	M 3	-	6	8	10	12	16	-	-	8	10,5	18,5	2	16,5	3	
22	M 4	M 5	12	16	20	25	32	-	-	8	10,5	18,5	2	16,5	3	
30	M 4	-	12	16	20	25	32	-	-	10	13	24,5	4	22	3,5	
30	M 5	M 6	12	16	20	25	32	40	50	10	13	24,5	4	22	3,5	
45	M 4	-	12	16	20	25	32	-	-	10	13	24,5	4	22	3,5	
45	M 5	M 6	12	16	20	25	32	40	50	10	13	24,5	4	22	3,5	
63	M 6	M 8	16	20	25	32	40	50	63	13,5	17,5	31	6,5	28,5	4	
78	M 8	M 10	20	25	32	40	50	63	80	16	21	36	8	34	4	

Specification

- Handle
 - Zinc die casting
- Powder coated
 - Black, RAL 9005, textured finish
 - Orange, RAL 2004, textured finish
 - Red, RAL 3000, textured finish
 - Silver, RAL 9006, textured finish
- Threaded stud and retaining screw
 - Steel
 - Zinc plated, blue passivated
- RoHS



Information

Adjustable hand levers GN 302.2 have a straight lever, not inclined, being parallel to the clamping space.

Adjustable hand levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Flat Adjustable Hand Levers GN 302 (Threaded Stud Steel, Blackened)
→ Page QVX
- Flat Adjustable Hand Levers GN 302.1 (Threaded Stud Stainless Steel)
→ Page QVX
- Adjustable Hand Levers GN 300.2 (Threaded Stud Steel, Zinc Plated)
→ Page QVX

How to order	1	l ₁
	2	d ₁
	3	l ₂
	4	Color

GN 302.2-78-M8-25-RS