



ROSTFREI  
Inox  
Stainless  
Steel

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> Length l						b <sub>1</sub>	b <sub>2</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
28	200	250	300	400	500	600	25	14	M 8	50	66	15

**Specification**

**Handle tube**

Stainless steel AISI 304, wall thickness 2 mm  
Ground, matte shiny finish

**Handle legs**

Stainless steel precision casting AISI CF-8  
Matte shot-blasted

RoHS

With the tubular handles GN 333.7, the handle legs and the handle tube are pressed together.

**see also...**

	Page
GN 333.6 Tubular Handles (Angled)	QVX
GN 426.5 Cabinet U-Handles	QVX
GN 565.5 Cabinet U-Handles (Mounting from the Back or the Operator's Side)	QVX
GN 666.5 Stainless Steel Tubular Handles (Mounting from the Back)	QVX
GN 333.1 Tubular Handles (Aluminum, Zinc Die Casting)	QVX

**Technical Information**

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order

GN 333.7-28-400

<sup>1</sup> d <sub>1</sub>
<sup>2</sup> Length l