




- 4 Type**
- C** With tapped hole, without bushing
 - E** With tapped bushing

2	3										3				
d ₁	d ₂ KU Type C					d ₃ KU Type E					d ₄ ≈	h ≈	t ₁ min.	t ₂ min.	
					KT Type C				KT Type E						
10	M 3	-	-	-	-	-	-	-	-	-	5	9,3	5	-	
12	M 4	-	-	-	-	-	-	-	-	-	6	11,2	6	-	
16	M 4	M 5	-	M 4	M 5	M 4**	-	M 4	M 5	M 5	8	15	6	6	
20	M 5	M 6	-	M 5	M 6	M 5	-	M 5	M 6	M 6	12	18	7,5	7,5	
25	M 5	M 6	M 8	M 6	M 8	M 6	M 8*	M 6	M 8	M 8	15	22,5	9	9	
30	M 6	M 8	-	-	-	-	-	-	-	-	15	28	12	-	
32	M 6	M 8	M 10	M 8	M 10	M 8	-	M 8	M 10	M 10	18	29	12	12	
35	M 8	M 10	-	-	-	-	-	-	-	-	18	32,5	15	-	
40	M 8	M 10	M 12	M 10	M 12	M 10	M 12*	M 10	M 12	M 12	22	37	15	15	
50	M 10	M 12	-	-	-	M 12	-	-	-	-	28	46	18	18	

* This size is only available in black with bushing in steel. ** This size is only available in black with bushing in brass.

Specification

1	5
Plastic, Phenolic resin (PF)	KU
• Flash removed and polished finish	● —
• Black	● RT
• Red, similar RAL 3003	
• Bushing (Type E)	—
- Steel, zinc plated	
- Brass (only in black)	MS
Plastic, Polyamide (PA)	KT
• Shock resistant	● —
• Black, matt	● RT
• Red, similar RAL 3003	
• Bushing (Type E)	
Steel, zinc plated	

RoHS

Technical Information	Page
Plastic Characteristics	QVX

Ball knobs DIN 319 in sizes 30 and 35, as well as various thread of type C and ball knobs made of technopolymer (KT) are not on the official DIN standard sheet.

see also...	Page
DIN 319 Ball Knobs (Press-On Type)	QVX
GN 319.1 Ball Knobs (Press-On Type)	QVX
DIN 319 Ball Knobs (Steel / Stainless Steel / Aluminium)	QVX

How to order (Black, without bushing)	
1	Material
2	d ₁
3	d ₂
4	Type

How to order (Red, with bushing steel)	
1	Material
2	d ₁
3	d ₃
4	Type
5	Color

How to order (Black, with bushing brass)	
1	Material
2	d ₁
3	d ₃
4	Type
5	Bushing