


elesa
Original design MMT.



d₁	l₁ ±0,5	l₂	b	d₂	d₃	h₁	h₂	h₃	h₄	t min.
10	120	94	16	M 5	18	53	43	8	24	12
10	180	94	16	M 5	18	56	43	8	24	12

Specification

Handle

Steel
Matte chrome-plated

Insulation

Plastic, Polyamide (PA)
• Glass fiber reinforced
• Operating temperature -30 °C to +150 °C
• Black, matte finish

RoHS

Cabinet U-handles GN 425.7 made of steel feature a plastic grip which, owing to its insulating properties, allows it to be used under high surface temperatures.

The above temperature distribution curve has been measured at a surface temperature of 200 °C and a room temperature of 23 °C.

see also...

GN 425 Cabinet U-Handles (Steel) Page

QVX

Technical Information

Plastic Characteristics QVX

How to order

GN 425.7-10-120

1 d₁

2 l₁