



4 Type

- A With handle locking in the folded up or folded down position
- B With spring return of the handle to the folded down position

1

l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	m ₁	m ₂
100	150	65	121	122	60	134	49
120	170	65	141	142	60	154	49

Specification

2

3

Handle bar

- Steel, chrome-plated
- Stainless steel AISI 303
- Matte shot-blasted

CR
NI

Handle tray

Zinc die casting
Powder coated

- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

● SW
● SR

RoHS

The folding handles with recessed tray GN 425.8 are used if the handle is to protrude by a maximum of 3 mm when folded down.

In type A, the folding handle is held in both end positions by spring-loaded thrust pieces.

In type B, the folding handle always spring-returns to the starting position after being released, preventing it from protruding with potentially interfering effect.

see also...

Page

GN 825.2 Folding Handles with Recessed Tray (Plastic, with Spring-Loaded Return)	QVX
GN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Installation dimensions	QVX
Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order

1	l ₁
2	Material (Handle bar)
3	Finish (Handle tray)
4	Type

GN 425.8-120-CR-SW-A



Installation dimensions

