



4 Type

A 2x2 bores for countersunk screws



Bores for countersunk screw DIN 7991

Swiveling range



2

3

l_1	l_2	d	h_1	h_2	h_3	h_4	$h_5 \approx$	l_3	l_4	m_1	m_2
60	60	8,3	18,5	7,5	9,5	19	35	20	45	36	36

Specification

1

5

- Zinc die casting **ZD**
- Powder coated
- Black, RAL 9005, textured finish **● SW**
- Silver, RAL 9006, textured finish **● SR**
- Guide sleeve
- Plastic (Polyacetal POM)
- Temperature resistant up to 80 °C
- Adjustable hand levers
 - Zinc die casting
 - Powder coated
 - Black for SW
 - Silver for SR
- Threaded stud and retaining screw
- Steel zinc plated, blue passivated
- Load Rating Information* → Page 2126
- Plastic Characteristics* → Page 2158
- RoHS

Information

With GN 437.2 Hinges, doors and covers can be secured at any desired angular position.

In its rest position, the hand lever is not connected to the locking thread of the hinge axis, i.e., it can be freely rotated. The serration only engages when the handle is pressed down, allowing the hinge to be clamped.

This prevents the engagement from releasing unintentionally. It additionally ensures that the hand lever does not hinder the movement of the door or cover.

To adjust to the door or cover, the clamp must be disengaged before the hinge can be swung into the new position.

see also...

- List of Hinge Types → Page 1284 ff.
- Hinges GN 437.1 → Page 1299
- Hinges GN 151.2 (Lockable, Plastic) → Page 1397

Accessory

- Stainless Steel Spacer Plates GN 2370
→ Page 1350
- Stainless Steel Plates GN 2372
→ Page 1351

How to order

1	Material
2	l_1
3	l_2
4	Type
5	Color

GN 437.2-ZD-60-60-A-SR