




Type EE



Type ES



Type SS



ROSTFREI
Inox
Stainless
Steel

4 Type

EE With 2 internal threads

ES With internal thread / threaded stud

SS With 2 threaded studs

d ₁	Type EE				Type ES				Type SS				d ₂	Length l	s	t ≈	
	h				h				h							GN 351	GN 451
8	8	13	-	-	8	13	-	-	8	13	-	-	M 3	6	1	3	3
10	10	15	20	-	10	15	20	-	10	15	20	-	M 4	10	1,2	4	4
15	10	15	20	-	10	15	20	25	10	15	20	25	M 4	10	1,4	4	4
20	15	20	25	-	15	20	25	30	15	20	25	30	M 6	18	2	6	6
25	20	25	30	-	15	20	30	-	15	20	30	-	M 6	18	2	6	6
30	20	30	40	-	15	20	30	40	15	30	40	-	M 8	20	2	8	8
40	20	30	40	-	20	30	40	-	20	30	40	-	M 8	23	2	8	8
50	30	40	50	-	20	30	40	50	20	30	40	50	M 10	28	2	10	8
60	30	40	50	-	30	40	50	-	30	40	50	-	M 10	28	2	10	8
70	30	45	-	-	30	45	-	-	30	45	-	-	M 10	27	3	10	8
75	30	40	55	-	25	40	55	-	25	40	55	-	M 12	37	3	12	11
100	40	55	75	-	40	55	75	-	40	55	75	-	M 16	41	3	16	14
125	55	75	-	-	55	75	-	-	55	75	-	-	M 16	41	3	16	14

* not available from stock, requires a minimum order quantity

Specification

- Natural rubber (NR), black
 - Vulcanized to the cover plates
 - Temperature resistant up to 80 °C

GN 351

Cover plates, threaded bushings / studs
Steel, zinc plated, blue passivated

Rubber hardness Shore A ±5

Soft	40
Medium	55
Hard	70

GN 451

Cover plates, threaded bushings / studs
Stainless steel AISI 304

Rubber hardness Shore A ±5

Soft*	40
Medium	55
Hard*	70

• *Elastomer Characteristics* → Page 2158

• *Stainless Steel Characteristics* → Page 2166

• RoHS

Information

Rubber buffers GN 351 / GN 451 are suitable for the elastic mounting of machine units such as motors, compressors and pumps.

see also...

• *Resilient Characteristics* → Page 2134 ff.

• *Buffers GN 353 / GN 453* → Page 1526 / 1527

On request

- Rubber in gray

How to order (Steel)

1	d ₁
2	h
3	d ₂
4	Type
5	Hardness

GN 351-30-30-M8-EE-55

How to order (Stainless steel)

1	d ₁
2	h
3	d ₂
4	Type
5	Hardness

GN 451-100-40-M16-ES-55