




- 3

Type
- F With fixed handle
- D With revolving handle

1	2		2									
Length l	s H11		e min.		d ₁ H7	d ₂	h ₁	h ₂	h ₃ ≈	h ₄ ≈		Ø
	Square		(Column 1)	(Column 2)						Type D	Type F	
63	V 10	-	13,1	-	-	20	20	11	15	54,5	50	16
80	V 10	V 12	13,1	16,1	B 8	24	24	13	18	61	56	18
100	V 12	V 14	16,1	18,1	B 10	28	28	13	21	67	64	20
125	V 14	V 17	18,1	22,2	B 10	34	34	14	26	76	72	22
160	V 17	V 19	22,2	25,2	B 14	38	38	14	29	83	80	25
200	V 19	V 22	25,2	28,2	B 17	44	44	21	34	96,5	90	28
250	V 22	V 24	28,2	32,2	B 17	48	48	21	36	105,5	100	32

Specification

- Body

Cast iron (GGG)

• Powder coated

Black, textured finish

• Face of the hub machined
- Fixed Handle DIN 39 for type F

Steel

Zinc plated, blue passivated
- Revolving Handle DIN 98 for type D

Steel

Zinc plated, blue passivated
- RoHS

The hub bores d ₁ H7 are not provided for in the official standard sheet.	
see also...	Page
DIN 468 Cranked Handles (cranked)	QVX
Technical Information	
Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX

How to order	1 Length l
DIN 469-125-V17-D	2 s (d ₁)
	3 Type