



- 4 Type (Base plate)**
- A0** Without rubber pad
  - B0** Without rubber pad, with 2 mounting holes
  - A1** With rubber pad, clipped on, black
  - A3** With rubber pad, rubber vulcanized, black

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>			Version								l <sub>7</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>6</sub>	m	s
		Version S / SK	Version U / UK	Version S / SK	Version U / UK	Version S / SK	Version U / UK	Version S / SK	Version U / UK	Version S / SK	Version U / UK	Version S / SK						
40	M 8	40	50	63	-	-	-	-	-	-	-	-	25	5,4	2	3,5	30	1,5
40	M 10	50	60	80	100	-	-	-	-	-	-	-	28	5,4	2	3,5	30	1,5
40	M 12	60	80	100	125	-	-	-	-	-	-	-	31	5,4	2	3,5	30	1,5
40*	M 16	-	-	-	-	75	100	125	150	200	250	37	5,4	2	3,5	30	1,5	
50	M 8	40	50	63	-	-	-	-	-	-	-	-	25	6,6	2,5	4	38	2
50	M 10	50	60	80	100	-	-	-	-	-	-	-	28	6,6	2,5	4	38	2
50	M 12	60	80	100	125	-	-	-	-	-	-	-	32	6,6	2,5	4	38	2
50	M 16	-	-	-	-	75	100	125	150	200	250	37	6,6	2,5	4	38	2	
60	M 8	40	50	63	-	-	-	-	-	-	-	-	25	6,6	2,5	4,5	48	2
60	M 10	50	60	80	100	-	-	-	-	-	-	-	28	6,6	2,5	4,5	48	2
60	M 12	60	80	100	125	-	-	-	-	-	-	-	32	6,6	2,5	4,5	48	2
60	M 16	-	-	-	-	75	100	125	150	200	250	37	6,6	2,5	4,5	48	2	
80	M 8	40	50	63	-	-	-	-	-	-	-	-	26	8,6	3	5	64	2
80	M 10	50	60	80	100	-	-	-	-	-	-	-	29	8,6	3	5	64	2
80	M 12	60	80	100	125	-	-	-	-	-	-	-	32	8,6	3	5	64	2
80	M 16	-	-	-	-	75	100	125	150	200	250	38	8,6	3	5	64	2	
80	M 20	-	-	-	-	75	100	125	150	200	250	45	8,6	3	5	64	2	
80	M 24	-	-	-	-	100	125	150	200	300	-	-	8,6	3	5	64	2	

**Specification**

\* not available in type B0

- Base plate  
Steel, zinc plated, blue passivated
- Threaded stem  
Steel, zinc plated, blue passivated
- Hex nut ISO 4032  
Steel, zinc plated, blue passivated
- Rubber pad, clipped on  
Black, TPE (Santoprene®)  
≈ 80 Shore A
- Rubber pad, vulcanized  
Black, NBR (Perbunan®)  
70±5 Shore A
- Load Rating Information → Page 2144
- Plastic Characteristics → Page 2158
- RoHS

**Versions of threaded stem**

<p><b>S</b> Without nut <b>SK</b> With nut</p>	<p><b>U</b> Without nut <b>UK</b> With nut</p>	<p><b>X</b> With internal thread</p>
<p>External hex at the bottom at <math>d_2</math> M 8, M 10, M 12</p>	<p>Hex socket at the top and wrench flat at the bottom at <math>d_2</math> M 16, M 20, M 24</p>	<p>External hex with internal thread at <math>d_2</math> M 8, M 10, M 12, M 16, M 20</p>

$d_1$	$d_2$	$h_3$	$h_4$	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>7</sub>	t
40	M 8	11	-	17	-	-	14	8
40	M 10	11	-	17	-	-	14	10
40	M 12	11	-	17	-	-	17	12
40	M 16	-	17	-	12	8	22	16
50	M 8	11	-	17	-	-	14	8
50	M 10	11	-	17	-	-	14	10
50	M 12	11	-	17	-	-	17	12
50	M 16	-	17	-	12	8	22	16
60	M 8	11	-	17	-	-	14	8
60	M 10	11	-	17	-	-	14	10
60	M 12	11	-	17	-	-	17	12
60	M 16	-	17	-	12	8	22	16
80	M 8	12	-	17	-	-	14	8
80	M 10	12	-	17	-	-	14	10
80	M 12	12	-	17	-	-	17	12
80	M 16	-	18	-	12	8	22	16
80	M 20	-	19	-	15	10	27	20
80	M 24	-	22	-	19	12	-	-

**Information**

Leveling feet GN 40 can be used in a host of combinations of base plates and adjustable spindle versions.

The base plate with the rubber pad protects sensitive surfaces and reduces lateral slippage. The type B0 can also be fastened to the mounting surface through two holes.

The leveling feet are supplied fully assembled and are not removable.

see also...

- *Leveling Feet GN 42 (Steel, with Fixing Lug, Drop Shape)* → Page 1460
- *Leveling Feet GN 41 (Stainless Steel, without Fixing Lug)* → Page 1462
- *Leveling Feet GN 43 (Stainless Steel, with Fixing Lug)* → Page 1470 / 1472
- *Leveling Feet GN 44 / GN 45 (Stainless Steel, without / with Fixing Lug)* → Page 1464 / 1474
- *Insert Bushings GN 448 (Plastic, for Tubes)* → Page 1498 / 1499
- *Insert Bushings GN 992 / GN 992.5 (Aluminum / Stainless Steel, for Tubes)* → Page 1501

**How to order**

1	$d_1$
2	$d_2$
3	$l_1$ ( $l_7$ )
4	Type (Base plate)
5	Version (Stem)

**GN 40-80-M12-100-A1-SK**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

