



<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>	<b>b</b>	<b>d<sub>3</sub></b>	<b>d<sub>4</sub></b>	<b>d<sub>5</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub> ≈</b>	<b>t min.</b>
63	M 6	7	16	16,8	12	41	12	12
80	M 8	9	21	21,8	17	52	15	16
100	M 10	11	25	25,8	21	65	19	20

**Specification**

**Handle**

- Stainless steel precision casting AISI 316
- Matte finish (Ra < 0.8 µm) **MT**
- Polished finish (Ra < 0.8 µm) **PL**

**Sealing ring**

- H-NBR **H**
- EPDM **E**
- FKM **F**
- Operating temperature -25 °C to + 150 °C
- Operating temperature -40 °C to + 120 °C
- Operating temperature -5 °C to +200 °C
- FDA compliant material
- Blue
- Hardness 85 ±5 Shore A

RoHS

T-handles GN 5064 comply with the DGUV testing principles and are intended for use in hygienic areas. The versions with PL finish, as well as with sealing ring H and E are additionally certified according to the guidelines of the EHEDG. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high-quality finish prevents the accumulation of dirt and facilitates cleaning.

T-handles are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces.

The T-handles can also be used in particularly aggressive environments thanks to the material used.

see also...	Page
GN 563.2 T-Handles (Aluminum)	QVX
GN 5063 T-Handles (Stainless Steel)	QVX
GN 8341 Wing Nuts (Stainless Steel, Hygienic Design)	QVX
GN 563 T-Handles (Plastic)	QVX
GN 563.1 T-Handle Screws (Plastic)	QVX

**Technical Information**

Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

**Accessory**

GN 7600 Sealing Rings	QVX
-----------------------	-----

How to order	
<b>1</b> <b>d<sub>1</sub></b>	
<b>2</b> <b>d<sub>2</sub></b>	
<b>3</b> <b>Finish</b>	
<b>4</b> <b>Material (Sealing ring)</b>	

**GN 5064-63-M6-PL-E**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4