



d ₁		Length l ±0,25			d ₂	d ₃	h ₁	h ₂	h ₃	h ₄	r	s max.
Stainless steel	Steel											
6	-	55*	64	88*	M 6	12	21	27,5	9,5	10	6	4
10	10	100	120	180	M 10 x 1	18	34	43	14	14	12	6

* Suitable for 19" rack and enclosure layout

Specification

Handle

• Steel	ST	
• Chrome plated		● CR
• Stainless steel AISI 303	NI	
• Matte shot-blasted finish		GS

Hex nuts ISO 8675

Stainless steel

Washers DIN 125

Stainless steel

RoHS

Folding handles GN 425.2 are used in places where the handle must not protrude or protrude only a short distance.

In both positions the handle is retained by a spring loaded detent.

see also...

	Page
GN 425.5 Folding Handles (Steel, Plastic Attachment Part)	QVX
GN 425.8 Folding Handles with Recessed Tray (with Handle Locking or Spring-Loaded Return)	QVX
GN 425.9 Folding Handles (Stainless Steel, With / Without Retaining Spring)	QVX
GN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Load Rating Information

QVX

Stainless Steel Characteristics

QVX

How to order (Steel)

1	Material
2	d ₁
3	Length l
4	Finish

GN 425.2-ST-10-120-CR

How to order (Stainless Steel)

1	Material
2	d ₁
3	Length l
4	Finish

GN 425.2-NI-10-180-GS