




elesa
Original design VRTP. / VRTP+I



- 2

Bore code
- B

Without keyway
- K

With keyway DIN 6885-1 P9
- 4

Type
- A

Without handle
- R

With revolving handle

1 d₁	3 d₂ H7 Bore		b	d ₃	d ₄	d ₅	l ₁	l ₂	l ₃	r	Ø Handle
80	8	10	18	18	20,5	25	17	35	45	29	16
100	10	12	20	18	20,5	25,5	17	37	60	37	18
125	12	14	22	22	26	31	22	44	65	48	22
160	14	16	25	26	31	40	27	51	73	65	23
200	16	20	28	30	36	48,5	34	61	80	84	24
250	20	24	32	35	44	58	38	69	90	105	25
300	20	26	35,5	40	52	66	43	78	90	127	25
375*	26	-	39	35	70	81	43	87	90	160	25

* not available from stock, requires a minimum order quantity

Specification

- Wheel body

Plastic, Polypropylene (PP)

• Reinforced, shock-resistant

• Operating temperature 0 °C to +80 °C

• Black, matte finish
- Hub bushing

Steel, blackened
- Cover

• Aluminum

- Anodized, natural color

- Self-adhesive

• Plastic, Polyester (PBT) for size 375

Gray, shiny finish
- Threaded bushing

Brass
- Revolving handle

Plastic, Polyamide (PA)

• Black, matte finish

• Spindle steel

Zinc plated, blue passivated

RoHS

On request

- with mushroom shaped handle GN 597.1

Elegant design and ergonomic requirements are realised for the spoked handwheels GN 522.

see also...	Page
GN 597.1 Revolving Mushroom Shaped Handles	QVX
Technical Information	
Keyways P9 DIN 6885-1	QVX
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Accessory	
GN 184 Countersunk Washers (for axial fixation)	QVX

How to order	1 d ₁
	2 Bore code
	3 d ₂
	4 Type
GN 522-125-B12-R	