



3 Type

- A** Mounting from the back with thread
- B** Mounting the operator's side with through hole
- C** Mounting from the operator's side by welding

4 Identification no.

- 1** Handle 90° foldaway
- 2** Handle 90° foldaway, with retaining springs
- 3** Handle 180° foldaway
- 4** Handle 180° foldaway, with retaining springs

1

Length l	b ₁	b ₂	b ₃	d ₁	d ₂	h ₁	h ₂ ≈	h ₃	h ₄	m	t ₁	t ₂
120	124	20	106	M 6	6,4	16	53	49	59	60	10	9,6

Specification

2

5

Attachment part

Stainless steel
 precision casting AISI CF-8
 • Matte shot-blasted finish
 • Powder coated
 Black, RAL 9005, textured finish only in type A and B

NI

GS

● SW

Handle bar

Stainless steel AISI 304
 Matte shot-blasted

Retaining springs

Spring steel AISI 301

RoHS

Folding handles GN 425.9 are used where the handle must only protrude a short distance in the resting position.

Folding handles numbers 1 and 2 are suitable for side “access,” as these have a 90° limit stop. If used from above, numbers 3 and 4 with a handle which can fold freely through 180° are a better version.

The retaining springs of numbers 2 and 4 keep the handle in any position. This keeps the handle in a position which can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

see also...

	Page
GN 425.8 Folding Handles with Recessed Tray (Steel / Stainless Steel, with Handle Locking or Spring-Loaded Return)	QVX

Technical Information

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order

1	Length l
2	Material
3	Type
4	Identification no.
5	Finish

GN 425.9-120-NI-A-1-SW