



3 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side

d₁	l₁ ±0,5 Type A	±0,3 Type B Threaded bore for mounting stud	d₂	d₃	h₁	h₂	l₂	r ≈	t₁	t₂
20	200	200	M 8	-	105	68	20	22	15	-
20	300	300	M 8	-	105	68	20	22	15	-
28	250	250	M 10	32	128	90	20	32	-	17
28	350	350	M 10	32	128	90	20	32	-	17
28	500	500	M 10	32	128	90	20	32	-	17

Specification

Handle

Stainless steel AISI 304

- d₁ = 20: Solid material
- d₁ = 28: Tube Ø 28 x 2
- Matte shot-blasted

Threaded bushing / Mounting stud

Stainless steel AISI 303

Grub screw for type B

Stainless steel

- d₁ = 20: DIN 914-M5-6-NI
- d₁ = 28: DIN 914-M6-8-NI

RoHS

Cabinet U-handles GN 426.6 can be mounted from the back (type A) as well as from the operator's side (type B).

In this case the stud is first screwed in from the machine side and then the handle is pushed on and secured with the grub screw.

Both mounting methods allow the mounting of a pair of handles in opposite position. This method could be used e.g. on doors (double handle). In general, a mounting stud with special length l₂ might be required.

see also...

Page

GN 425.1 Cabinet U-Handles (Ø 8, 10, 12 / Aluminum / Stainless Steel, Angled) QVX

Technical Information

Load Rating Information

QVX

Stainless Steel Characteristics

QVX

How to order

GN 426.6-20-300-A

1	d ₁
2	l ₁
3	Type