



elesa

Original design VRTP-P+I-SST

Inox
Stainless
SteeliF product
design
award**2 Bore code****B** Without keyway**K** With keyway DIN 6885-1 P9**4 Type****R** With revolving handle**1****3**

d ₁	d ₂ H7	d ₃	d ₄	d ₅	b	l ₁	l ₂	l ₃	r	Ø Handle
80	8	18	20,5	25	18	17	35	45	29	16
100	10	18	20,5	25,5	20	17	37	60	37	18
125	12	22	26	31	22	22	44	65	48	22
160	14	26	31	40	25	27	51	80	65	23
200	16	30	36	48,5	28	34	61	80	84	24

Specification**Wheel body**

Plastic, Polypropylene (PP)

- FDA compliant plastic granulate
- Reinforced, shock-resistant
- Operating temperature 0 °C to +80 °C
- Black, matte finish

Hub bushing

Stainless steel AISI 304

Cover

Stainless steel AISI 304

Self-adhesive

Revolving handle

Plastic, Polyamide (PA)

- FDA compliant plastic granulate
- Black, matte finish
- Spindle
Stainless steel AISI 304

RoHS

Elegant design taking account of ergonomic and hygienic requirements are the outstanding features of spoked handwheels GN 522.5.

Owing to the materials used, they are especially suitable for use in corrosive atmospheres or in areas which must be wet cleaned. In particular, the FDA certified plastic materials allow the use in the food industry.

Technical Information

Keyway P9 DIN 6885-1

Cross holes GN 110

ISO Fundamental Tolerances

Plastic Characteristics

Stainless Steel Characteristics

Page

QVX

QVX

QVX

QVX

QVX

Accessory**GN 184.5** Countersunk Washers (for Axial Fixing)

QVX

How to order
GN 522.5-125-B12-R
1 d₁**2** Bore code**3** d₂**4** Type