



**3** Type

- E** With threaded blind bore
- D** With threaded through bore

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Type E			<b>3</b> d <sub>3</sub> Type D			d <sub>4</sub>	b	h	t <sub>1</sub> min.	t <sub>2</sub>
20	M 4	-	-	-	-	-	-	9,5	11	6	-
26	M 5	M 6	-	-	-	-	-	11	13	6	-
32	M 5	M 6	M 8	M 5	M 6	-	6,5	13	15	6	12
40	M 5	M 6	M 8	M 5	M 6	M 8	9	15,5	17	6	12
48	M 8	-	-	M 8	-	-	9	19	19	10	16
56	M 10	-	-	M 10	-	-	11	21	23	13	20

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 130 °C  
- Black, matte finish
- Bushing  
Brass
- *Plastic Characteristics* → Page 2158
- RoHS

**Information**

- see also...
- *Wing Nuts GN 532.1 (with Protruding Hub)* → Page 616
  - *Wing Nuts GN 634* → Page 606
  - *Wing Nuts GN 640* → Page 612

How to order

**GN 532-40-M8-E**

- 1** d<sub>1</sub>
- 2** d<sub>2</sub> (d<sub>3</sub>)
- 3** Type