



1 d ₁	2 d ₂	3 Length l										d ₃	d ₄	h ₁	h ₂ ≈	
25	M 4	-	6	10	-	-	-	-	-	-	-	-	13	8	19	8
25	M 5	M 6	10	16	20	25	30	40	-	-	-	-	13	8	19	8
32	M 6	-	16	20	25	30	40	-	-	-	-	-	15	10	23	10
32	M 8	-	16	20	30	40	50	-	-	-	-	-	15	10	23	10
40	M 6	-	20	25	30	-	-	-	-	-	-	-	17	13	27	12
40	M 8	-	16	20	25	30	35	40	45	50	55	70	17	13	27	12
40	M 10	-	20	25	30	40	50	-	-	-	-	-	17	13	27	12
50	M 8	-	16	20	25	30	40	50	-	-	-	-	19	15	32	14
50	M 10	M 12	20	30	40	50	60	-	-	-	-	-	19	15	32	14
63	M 10	M 12	20	30	40	50	60	-	-	-	-	-	22	19	37	16
74	M 12	-	30	50	70	-	-	-	-	-	-	-	26	17	43,5	22
74	M 14	-	50	-	-	-	-	-	-	-	-	-	26	17	43,5	22
74	M 16	-	30	40	50	60	70	-	-	-	-	-	26	17	43,5	22
84	M 12	M 16	30	50	70	-	-	-	-	-	-	-	28	22	44	21
95	M 16	-	50	-	-	-	-	-	-	-	-	-	32	19	46	21

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Reinforced, shock-resistant
- Temperature resistant up to 90 °C
- Black, matte finish
- Threaded stud
Steel
Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- RoHS

On request

- Cover caps in other colors (standard color: black)

Information

see also...

- *Star Knobs with Threaded Stud GN 5337.7 (Threaded Stud Stainless Steel)* → Page 563
- *Star Knobs with Threaded Stud GN 5337.4 (Threaded Stud Stainless Steel)* → Page 565
- *Softline Star Knobs with Threaded Stud GN 5337.6* → Page 567
- *Star Knobs with Threaded Stud GN 5337.2 with Loss Protection GN 111.7* → Page 2084

How to order

GN 5337.2-50-M10-20

1	d ₁
2	d ₂
3	Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

