



Length l	d ₁ H7 Bore	s H11 Square	d ₂	d ₃	h ₁	h ₂ ≈	h ₃	h ₄	h ₅ ≈	Ø Handle
80	B 10	V 10	23	30	19,5	4	25,5	4,3	43	16
100	B 12	V 12	26,7	35	23,5	5,5	29,5	4,2	57,5	18
125	B 14	V 14	28	37	30,5	10,5	36,5	4,2	76,5	24

Specification 3

Body

Aluminum

- Plastic coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish
- Contact face of hub machined

● SW
● SR

Cover

Plastic

Light grey

Retractable handle GN 798.3

Plastic, Polyamide (PA)

- Black, matt finish
- Retractable mechanism
- Steel, blackened

Retractable handle GN 798.5

Plastic, Polyamide (PA)

- Black, matt finish
- Retractable mechanism
- Stainless steel
- Spindle, AISI 303
- Flat base, AISI 316 LHC
- Sintered

RoHS

The handpiece of the cranked handle GN 472.3 / GN 472.5 is locked in a tapered bore in the operating position.

For tilting, the handle must first be pulled out of the taper in axial direction.

A compression spring holds the handle in both end positions. When folded out, it automatically re-engages.

see also...

	Page
GN 471.3 Cranked Handles with Retractable Handle (Aluminium)	QVX
GN 570.3 Cranked Handles with Retractable Handle (Plastic)	QVX

Technical Information

Cross holes GN 110	QVX
Squares DIN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Retractable Mechanism Steel)

1 2 3
GN 472.3-100-V12-SR

1	Length l
2	s (d ₁)
3	Color

How to order (Retractable Mechanism Stainless Steel)

1 2 3
GN 472.5-125-B14-SW

1	Length l
2	d ₁ (s)
3	Color