



1

2

l_1	d_1				d_2	d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
42	M 5	M 6	-	-	12	18	16	27	6	32	3,5	10
63	M 6	M 8	-	-	15	23	20	34	8	43	4	14
80	M 8	M 10	M 12	-	19	28	24	42	10	54	4	17
100	M 10	M 12	M 14	M 16	25	33	31	48	12	65	5	20

Specification

3

- Handle
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 120 °C
- Black, RAL 9005, matte finish ● **SW**
- Threaded bushing
Brass
- Releasing button
Plastic, black
- *Plastic Characteristics* → Page 2158
- **RoHS**

On request

- With threaded bushing stainless steel
- Other colors

Information

Adjustable hand levers GN 503 are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swiveled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

Its use is, however, limited to applications where dismantling of the lever for installation is not required. The threaded insert can after disengagement be screwed in using the serration of the insert.

How to order

GN 503-80-M10-SW

- 1 l_1
- 2 d_1
- 3 Color