



ROSTFREI
Inox
Stainless
Steel

1.1
1.2
1.3
1.4

| 1 | | 2 | | 3 | | | | | | | | | | | |
|----------------|----------------|------|------|----------|----|----|----------------|----------------|----------------|----------------|----------------|----------------|-----------------------|--------|----|
| d ₁ | d ₂ | M 8 | M 10 | Length l | | | d ₃ | d ₄ | d ₅ | h ₁ | h ₂ | h ₃ | h ₄ Stroke | t min. | |
| 40 | M 6 | M 8 | | 20 | 25 | 32 | 40 | 13,5 | 18 | 13,5 | 30 | 14 | 7 | 2,5 | 11 |
| 50 | M 8 | M 10 | | 25 | 32 | 40 | 50 | 16 | 22 | 16,5 | 34 | 15 | 8 | 3,5 | 14 |

2.1

Specification

- Knob
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black, matte finish
- Color of the cover cap
Black, RAL 9005, matte finish
- Threaded bushing / threaded stud
- Steel **ST**
Blackened
- Stainless steel AISI 303 **NI**
- Annular gear
Zinc die casting
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- Cover caps in other colors

4

Information

Safety star knobs GN 5337.3 are most suitable for applications where an accidental or inconsiderate loosening or adjusting of the knob may lead to accidents.

In non-operative condition, the star knob is not linked with the threaded insert, i.e. the knob can be turned easily.

Only after axial pushing of the star knob, the two serrations get engaged so that the knob can be untightened resp. tightened.

After „releasing“, the two serrations are disengaged by a spring.

see also...

- Safety Tension Levers GN 312 → Page 496 / 497
- Safety Hand Levers GN 604.2 → Page 494 / 495

2.2

2.3

2.4

How to order (Bushing)

| | |
|---|----------------|
| 1 | d ₁ |
| 2 | d ₂ |
| 4 | Material |

GN 5337.3-40-M8-ST

How to order (Threaded stud)

| | |
|---|----------------|
| 1 | d ₁ |
| 2 | d ₂ |
| 3 | Length l |
| 4 | Material |

GN 5337.3-50-M10-40-NI