







Type V



Type F




Type S



3 Type

- V** With anti-twist protection
- F** With anti-twist protection, with spring
- S** Heavy

Use



Type V								
n	d				b	h ₁	h ₂	Length l
8	M 4	M 5	M 6	M 8	11,6	3,8	1	16
10	M 4	M 5	M 6	M 8	14	3,8	1,5	20

1

2

Type F

n	d				b	h ₁	h ₂	h ₃ ≈	Length l
8	M 4	M 5	M 6	M 8	11,6	3,8	1	8	16
10	M 4	M 5	M 6	M 8	14	3,8	1,5	12	20

Type S								
n	d				b	h ₁	h ₂	Length l
6	M 4	M 5	M 6	-	9,6	3	1	10
8	M 4	M 5	M 6	M 8	15,8	4	2	16
10	M 4	M 5	M 6	M 8	19,5	5,5	5	20

Specification

Steel

Zinc plated, blue passivated

RoHS



SZ

T-nuts GN 50b fasten attachments and accessories in the slot of aluminum profiles.

The spring of type F secures the T-nut against unwanted slipping in the groove, making installation easier.

T-nuts of types V and F can be swiveled into the slot at any position.

see also...

	Page
GN 10b Aluminum Profiles (Profile Type Light)	QVX
GN 10b Aluminum Profiles (Profile Type Heavy)	QVX

How to order

GN 50b-10 M8-V-SZ

1	n
2	d
3	Type
4	Material / Finish



Assembly Instruction

