



elesa
Original design IF / IFF

4 Type

- A With hand guard, one side
- B With hand guard, both sides

1 d ₁	2 d ₂	3 l ₂	d ₃	d ₄	l ₁	l ₃	l ₄	t
30	M 8	20	64	46	112	4	4	20
30	M 10	20	64	46	112	4	4	18

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Threaded bushing

Brass

Threaded stud

Steel
Zinc plated, blue passivated

RoHS

Cylindrical handles GN 539.2 are used as handles for electronic tools such as angle grinders, percussion drills etc. Their special feature is the hand guard on one or both sides.

see also...

	Page
GN 539 Fixed Cylindrical Handles	QVX
GN 519 Cylindrical Knobs (with Thread)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order (with threaded bushing)

GN 539.2-30-M8-A

1	d ₁
2	d ₂
3	Type

How to order (with threaded stud)

GN 539.2-30-M10-20-A

1	d ₁
2	d ₂
3	l ₂
4	Type