



1

2

d ₁	l ₂	d ₂	l ₁	l ₃	l ₄	h ₁	h ₂
M 4	14	7,5	22	9,5	4,5	18,5	23
M 4	16	7,5	22	11,5	4,5	18,5	23
M 4	20	7,5	22	15,5	4,5	18,5	23
M 5	16	9	30	10	6	24,5	30,5
M 5	20	9	30	14	6	24,5	30,5
M 5	25	9	30	19	6	24,5	30,5
M 6	20	10,5	45	13,5	6,5	24,5	35
M 6	25	10,5	45	18,5	6,5	24,5	35
M 6	30	10,5	45	25,5	6,5	24,5	35
M 6	32	10,5	45	25,5	6,5	24,5	35

Specification

- Handle
Zinc die casting
Powder coated
Silver, RAL 9006, textured finish
- Threaded insert / distance sleeve
Stainless steel AISI 303
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

For mounting clamps, the clamping kits GN 511 replace the socket cap screws with hexagonal socket DIN 912. It is used on all clamping points where repeated clamping actions are required, e.g. for adjusting a stop mechanism.

The matching clamping kits for each clamping thread are listed in the dimensional tables of the mounting clamps.

How to order

GN 511-M5-25

1 d₁2 l₂