



elisa
Original design VDT.



2 Bore code

- B Without keyway
- K With keyway

4 Type

- A Without handle
- D With revolving handle

1

3

d ₁	d ₂ H7 Bore	d ₃	d ₄	d ₅	d ₆	d ₇	d ₈	d ₉	b	h	l ₁ -0,5	l ₂ -0,5	l ₃	r	Ø Handle
100	10	22	20	25	27	35	54	32	22	5,5	22	49	60	37	18
125	12	26	24	29	31	44	70	37	25	7	27	58	65	47	22
160	14	35	33	37	39	55	90	46	27	11	28	64	80	62	24
200	20	40	38	48,5	50	66	110	51	30	9	31	67	90	78	25

Specification

- Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
 - Black, matte finish
- Hub bushing
Steel, blackened
- Threaded bushing
Brass
- Cover
Plastic
Black, matte finish
- Revolving handles
 - Plastic, Technopolymer
Black, matte finish
 - Spindle
Steel, zinc plated, blue passivated
- Keyway P9 DIN 6885 Page 1 → Page 2078
- Cross Holes GN 110 → Page 2080
- Plastic Characteristics → Page 2158
- RoHS

Information

Disk handwheels GN 524 are renowned in particular for their design and the matt passivated aluminium ring in the front and the shape of the handle.

The hub cap shrouds the fixing components such as screws, countersunk washers as well as the shaft end. The hub cap is inserted by pushing it on by hand. To remove it run a finger with little pressure along the edge of the cap.

see also...

- Countersunk Washers GN 184 (for Axial Fixing) → Page 1090
- Disk Handwheels GN 521 (Plastic, Hub Bushing Steel) → Page 254

How to order

GN 524 -125-B12-D

- | | |
|---|----------------|
| 1 | d ₁ |
| 2 | Bore code |
| 3 | d ₂ |
| 4 | Type |