




View of magnetic surface



2

Length <b>L</b>	<b>b</b>	<b>h</b>	Nominal magnetic force in N
55	22,5	8,5	48

**Specification**

- Magnet material  
NdFeB **ND**  
Neodymium, iron, boron  
Temperature resistant up to 80 °C

- Housing  
Plastic
  - White, RAL 9003 ○ **WS**
  - Gray, RAL 7040 ● **GR**
  - Black, RAL 9004 ● **SW**
  - Red, RAL 3031 ● **RT**

• RoHS

**Accessory**

- Holding Disks GN 70 → Page QVX
- Adhesive Disks GN 70.1 → Page QVX

**On request**

- Other colors
- Magnet material hard ferrite
- With custom imprint

**Information**

Magnets GN 53.2 work in combination with the flat, rectangular plastic housing as a system for holding documents, templates, drawings etc. that are used in technical environments.

The neodymium magnets used are characterized by a high retaining force.

see also...

- More Information on Retaining Magnets → Page QVX
- Magnets GN 53.1 → Page QVX
- Magnets GN 53.3 / GN 53.4 (Disk-Shaped, with Handle) → Page QVX / QVX

How to order

**GN 53.2-ND-55-GR**

1	Magnet material
2	Length <b>L</b>
3	Color

