



Square bushing
in brass



1

2

d ₁	s H9 Square		d ₂	d ₃	h ₁	h ₂	t
40	V 6	-	14	21	15	10	4
50	V 6	V 7	14	24	18	10	5
60	V 6	V 7	16	29	20	10	4
70	V 7	V 8	18	35	22	14	5
85	V 8	V 9	18	45	25	14	8
100	V 10	-	18	57	28	14	6

Specification

- Plastic
Duroplast (PF)
 - Temperature resistant up to 110 °C
 - Black, shiny finish
- Square bushing
Brass
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

Information

Star knobs GN 5333 meet highest quality requirements. Due to a special manufacturing process the mould parting line can be avoided.

How to order

GN 5333-50-V7

1 d₁

2 s