



1 Length l	2 d ₁ H7 Bore	2 d ₂ Thread		h ₁	h ₂	s Square	t min.
55	B 6	M 6	M 8	33	22	14	12
67	B 8	M 8	-	37	25	16	16
80	B 8	M 8	M 10	41	26	20	16

Specification

Aluminum

- Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish
- Plain finish, tumbled
- Flash mark not visible

- SW
- SR
- BL

RoHS

T-handles GN 563.2 can be used as either operating handles or for clamping purposes, producing high clamping forces.

T-handle screws are forged in a die and therefore have a structure with a higher stability and a smooth surface.

Original ELESA design, produced in metal in agreement with ELESA S.p.a.

see also...

GN 563 T-Handles (Plastic)

Page

QVX

Technical Information

ISO Fundamental Tolerances

QVX

How to order

GN 563.2-67-M8-SW

1	Length l
2	d ₂ (d ₁)
3	Finish