




elesa
Original design VC.192+F /
VC.192+IN

- 3 Type**
- S** With face and pointer
 - Z** With pointer

1 d₁ Type S	1 d₁ Type Z	2 d₂ H9 Bore	d₃	d₄	d₅	d₆	d₇	e	h₁	h₂	h₃	h₄	h₅	l₁	l₂
32	-	B 6	14	19	-	M 4	36	6	27	-	3	-	19	19	-
40	40	B 6	14	21	25	M 4	45	6	30	27	3	2	14	24	25
50	50	B 8	15	25	30	M 5	56	7	36	33	3	2	20	30	31
60	60	B 8	15	27	32	M 5	70	7	42	37	5	2	20	37	38
70	70	B 10	18	30	35	M 6	80	10	48	44	5	2	25	42	45

Specification

- Handle**
Plastic, phenolic resin (PF)
• Operating temperature -20 °C to +110 °C
• Black, shiny finish
- Pointer**
Plastic, Polyamide (PA)
• Operating temperature -20 °C to +110 °C
• Black, shiny finish
• Arrow for type S
White
- Bushing**
• d1 = 32, 40: Brass
• d1 = 50, 60, 70: Steel, blackened
- Grub screw DIN 916**
Stainless steel
with internal hex and serrated point
- RoHS

Setting knobs GN 5338 are very appealing with a good gripping feel. The manufacturing technique has made it possible to produce them with no visible flash mark.

The indicator element is slid onto the handle hub and secured against rotation.

Two studs with a serrated point ensure proper fastening on the shaft.

Technical Information	Page
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order	1 d ₁
GN 5338-50-B8-S	2 d ₂
	3 Type