



ROSTFREI
Inox
Stainless
Steel

1 d₁	2 d₂	3 Length l			d₃	h	k	t min.
20	M 5	10	16	-	14	13	8,5	8
24	M 6	16	20	25	16	15	10,5	9
28	M 8	16	20	30	18	17	12,5	10

Specification

- Stainless steel AISI 304
 - Matte shot-blasted
 - Highly polished
- *Stainless Steel Characteristics* → *Page 2166*
- *RoHS*

4

MT

PL

Information

The knurling of the knurled screws GN 535 and knurled nuts GN 536 allows a use in an environment with hygienic requirements.

see also...

- *Knurled Nuts DIN 6303 (Stainless Steel)* → *Page 642*
- *Knurled Nuts DIN 466 (Stainless Steel)* → *Page 646*
- *Knurled Screws DIN 464 (Stainless Steel)* → *Page 647*

How to order (Screw)		1	d ₁
		2	d ₂
		3	Length l
		4	Finish
GN 535-28-M8-20-MT			

How to order (Internal thread)		1	d ₁
		2	d ₂
		4	Finish
GN 536-20-M5-PL			