




elesa
Original design MT-AT

Length l	¹ ² d ₁ H9 Bore	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ ≈	t min.	Ø Handle
50	B 6	15	18	22,5	29,5	18,5	12,5	35	16	14
64	B 8	15	20	26,5	31,5	17,5	13,5	45	18	16
80	B 10	18	24	30	37	23,5	13,5	60	23	18
100	B 12	18	24	33,5	40,5	25	14	65	22	22
130	B 14	26	34	39	49	34	15	65	28	22
160	B 16	26	34,5	44	54,5	36	18	80	28	24

Specification

- Body**
Plastic, Polyamide (PA)
 - Glass fiber reinforced
 - Operating temperature 0 °C to +90 °C
 - Black, matte finish
- Hub bushing**
Steel, blackened
- Revolving handle**
Plastic, Polyamide (PA)
 - Black, matte finish
 - Spindle steel
 - Zinc plated, blue passivated

RoHS

Cranked handles GN 570.2 are connected to a shaft by means of a cross pin. Owing to the small, non-protruding steel bushing, these cranked handles are lower priced than GN 570.

see also...	Page
GN 570 Cranked Handles (Plastic)	QVX
GN 570.1 Cranked Handles (Plastic)	QVX
GN 471 Cranked Handles (Aluminum)	QVX
GN 471.1 Cranked Handles (Zinc Die Casting)	QVX

Technical Information	
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order

1

2

GN 570.2-80-B10

1

Length l

2

d₁