




elesa
Original design I.280 p



¹ d ₁	² d ₂	d ₃	l ₁	l ₂
18	M 6	15	40	16
21	M 8	17	50	16
23	M 10	19	65	16
26	M 10	21	80	16
28	M 12	22	90	16
31	M 12	25	102	16

Specification

Handle

- Plastic, phenolic resin (PF)
- Operating temperature -20 °C to +110 °C
- Black, shiny finish

Threaded stud

- Steel
- Zinc plated, blue passivated

RoHS

Fixed cylindrical handles GN 539 can be used as handles or to replace ball knobs on control levers. Instead of the threaded stud, the levers must then be provided with an internal thread.

The threaded stud is deeply embedded in the handle which greatly increases the strength of the plastic body.

see also...

	Page
GN 598 Revolving Handles	QVX
GN 519 Cylindrical Knobs (with thread)	QVX

Technical Information

Plastic Characteristics

QVX

How to order

GN 539-21-M8

1	d ₁
2	d ₂