



2 Bore code

B Without keyway

K With keyway DIN 6885-2 P9

Length l	d ₁ H7 Bore	d ₂	h	b P9	t
75	16	32	24	5	17,3
90	18	34	26	6	19,7
110	20	36	30	6	21,7
135	22	42	32	6	23,7
165	24	44	36	8	25,7

Specification

Body

Cast iron (GGG)

- Hub machined, flash
- Ground, shot-blasted

Handle

Steel, blackened

Indexing pin

Steel, hardened

RoHS

Indexing cranked handles GN 558 are for positioning mechanisms.

Other standard machine elements for positioning of spindles:

- Indexing Mechanisms GN 200
- Indexing Levers GN 215
- Adjustable Knobs GN 700 (with Stepless Positioning)

see also...

	Page
GN 200 Indexing Mechanisms	QVX
GN 215 Indexing Levers	QVX
GN 700 Adjustable Knobs (with Stepless Positioning)	QVX

Technical Information

Keyway P9 DIN 6885-2

ISO Fundamental Tolerances

How to order

GN 558-75-K16

1	Length l
2	Bore code + d1
3	d1