



b₁	a	b₂	h₁	h₂	Length l	A/F	Nominal magnetic forces in N
6	30	9,5	3	10,2	41	1,5	18
8	30	11,6	2,3	9,3	41	2	30
8	40	12,5	4,8	12,9	41	2	30
10	45	13,7	6	13,2	41	2	30

Specification

- Plastic Technopolymer (Polyamide PA) Black, matte finish ● **SW**
- Material of the magnet NdFeB Neodymium, iron, boron Temperature resistant up to 80 °C
- Steel insert, grub screw Zinc plated, blue passivated
- RoHS

Information

With GN 56 retaining magnets doors, covers or even tools and accessories can simply be attached to profile systems using magnets.

Thanks to the side-mounted plastic spring elements the retaining magnet can be introduced into a profile nut at any point. When affixed this way, the magnet holds with a multiple of its magnet nominal holding force in the nut. If necessary, the retaining magnet can be taken out of the nut again with a suitable screw driver via the recesses on the front.

Lightly turning the threaded pin against the groove base stops the retaining magnet from moving in the direction of the nut. Additional protection against sideward movement can be achieved with nuts for T-nuts GN 506, for example.

see also...

- Product Family Standard Parts for Profile Systems → Page 18
- More Information to Retaining Magnets → Page 2028

How to order	1
GN 56-6-30-SW	b ₁
	a
	Color

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

