


Type A





Type B



3 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side (only for $b_1 = 26$)



1

2

b_1	Length $l \pm 0,25$	a	b_2	b_3	b_4	$b_5 + 1$	d_1	d_2	h_1	h_2	r	t min.
20	112	13	24	32	50	13,5	M 6	-	32	48	13	10
20	128	13	24	32	50	13,5	M 6	-	32	48	13	10
26	128	17	32	34	57	18	M 8	M 6	34	54	17	12
26	160	17	32	34	57	18	M 8	M 6	34	54	17	12

Specification

4

Handle

Aluminum

- Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish
- Anodized, natural color
- Plain finish, tumbled

- **SW**
- **SR**
- **EL**
- **BL**

Fastening set for type B

Steel, zinc plated, blue passivated

- Socket button head screws ISO 7380-M6-25
- Hex nuts ISO 4032-M6
- Washers DIN 125

RoHS

Inclined cabinet U-handles GN 565.2 are manufactured from a bent aluminum profile. Their special features are their rigidity and ergonomic shaping. The angled contact surface allows improved access even in tight spaces such as corners.

For type B, socket button head screws, hex nuts and washers are included parts of the order.

see also...

Page

GN 565.7 Inclined Cabinet U-Handles (Stainless Steel, Mounting from the Back)	QVX
GN 425.1 Cabinet U-Handles (Steel / Aluminum / Stainless Steel, Angled)	QVX
GN 426.1 Cabinet U-Handles (Aluminum, Angled)	QVX
GN 630.1 Cabinet U-Handles (Polyamid)	QVX

Technical Information

Product Family Standard Parts for Profile Systems

QVX

Load Rating Information

QVX

How to order

GN 565.2-26-128-B-SW

- 1** b_1
- 2** Length l
- 3** Type
- 4** Finish