



Inox
Stainless
Steel



d ₁	d ₂	Length l	w Compression	Spring load in N ≈	
				Initial	End
M 6	3,5	14	0,9	12	17
M 8	5	16	1,5	20	35
M 10	6	19	1,9	25	45

Specification

- Housing
Plastic (Polyacetal POM)
Temperature resistant up to 50 °C
- Ball
 - Stainless steel AISI 420C **NI**
 - Plastic (Polyacetal POM) **P**
- Pressure spring
Stainless steel AISI 631
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS



Information

Plastic spring plungers GN 615.2 are used as detents as well as for push-on and push-off applications and ejectors.

These spring plungers are all stainless versions.

see also...

- *Spring Plungers GN 615 (with Ball, with Slot)* → Page 976

How to order

GN615.2-M6-NI

1 d₁

2 Ball material