





Original design I.701+x / I.731+x


Type

- A** Without finger molding
B With finger molding

 d_1	 d_2	 l_1	b	d_3	l_2
13,5	M 4	20	11	11	8
13,5	M 5	20	11	11	10
16	M 5	23	13	12,5	10

Specification**Knob**

Plastic, Polyamide (PA)

- Operating temperature -20 °C to +90 °C
- Black, matte finish

Spindle

Steel

Zinc plated

RoHS

Revolving knobs GN 595 are used e.g. in connection with small handwheels or cranked handles with low adjustment torque. Finger mouldings in type B provide additional safety against slipping and make operation easier.

Technical Information





Plastic Characteristics

Page

QVX

How to order



	d_1
	d_2
	l_1
	Type