



4 Type

- D** With threaded through bore
- E** With threaded blind bore

2 d_1	3 d_2	d_3	h_1	h_2	t_1 min.	t_2
32	M 6	12	20	9	12	10
40	M 8	14	25	13	15	13
50	M 10	18	32	18	18	16
63	M 12	20	40	23	22	20

Specification

- Stainless steel precision casting AISI 316 Polished **A4 PL**
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**



Information

Hand knobs GN 6335 satisfy the dimensions of the DIN 6335 but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygiene requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- *Hand Knobs DIN 6335 (Plastic)* → Page 586
- *Hand Knobs DIN 6335 (Cast Iron / Stainless Steel / Aluminum)* → Page 582
- *Hand Knobs GN 6335.1 (Duroplast, with Protruding Steel Bushing)* → Page 588
- *Hand Knobs GN 6335.2 (Technopolymer, with Protruding Steel Bushing)* → Page 588

How to order

1	Material
2	d_1
3	d_2
4	Type
5	Finish

GN 6335-A4-40-M8-E-PL