




elesa
Original design EBS+x



¹ d ₁	² d ₂	d ₃	d ₄ +0,5	l ₁	l ₂	l ₃ ≈	l ₄ ≈
45	M 10	12	32	64	17	1	22

Specification

Handle

- Plastic, polypropylene (PP)
- Operating temperature 0 °C to +80 °C
- Black, matte finish

Spindle

- Steel
- Zinc plated, blue passivated

RoHS

The revolving ball handle GN 596 is in general used where a pulling action is involved such as on vertically positioned handwheels.

see also...

GN 319.2 Revolving Ball Knobs

Page

QVX

Technical Information

Product Family Ergostyle®

QVX

Plastic Characteristics

QVX

Stainless Steel Characteristics

QVX

How to order

¹ ²
GN 596-45-M10

1 d₁

2 d₂