



d ₁	d ₂	l ₁ Nominal length						l ₂		d ₃		d ₄	h ₁	h ₂
		5	10	15	20	25	-	MS pivot	KU pivot	MS pivot	KU pivot			
25	M 5	10	15	20	25	-	0,5	1	3	3	12	16	8	
32	M 6	10	16	20	25	30	1	1,3	4	3,5	14	20	10	
40	M 8	20	25	30	40	50	1,5	1,6	6	5	18	25	13	
50	M 10	20	25	30	45	55	2	1,9	8	6,5	22	32	17	

Specification

- Star knob DIN 6336
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Threaded stud
Stainless steel AISI 304 Cu
- Pivot
 - Brass **MS**
 - Plastic (Polyacetal POM) **KU**
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Star knobs GN 6336.10 with brass or plastic thrust pad are used when indentations or damage is to be avoided.

see also...

- Knurled Screws GN 421.10 (with Pivot) → Page 638
- Wing Screws GN 633.10 (with Pivot) → Page 610
- Knurled Screws GN 7336.5 (with Pivot) → Page 627
- Star Knobs with Threaded Stud GN 6336.10 with Loss Protection GN 111.7 → Page 2084

How to order

GN 6336.10-32-M6-20-KU

1	d ₁
2	d ₂
3	l ₁
4	Material thrust pad