




Identification no. 1

Identification no. 2

Type K



elesa

Original design GCA-2 / GCA-4




1 Type

- K** Ball-shaped rollers
- Z** Cylindrical rollers
- ZA** Cylindrically offset rollers




2 Identification no.

- 1** Single row
- 2** Double row

Type Z




Type ZA



3

Length l	b ₁	b ₂	b ₃	d ₁	d ₂	d ₃	h ₁	Identification no. 1	Identification no. 2	h ₂	h ₃	Packaging unit
1440	3000	30,5	29,5	31,5	12,5	11,25	13,5	57	102,5	80	36	2



Specification



Carrier profile	AL
Aluminum	
Anodized, natural color	
Rollers	GR
Plastic, polyethylene (PE)	
• Operating temperature -20 °C to 90 °C	
• Gray, RAL 7035	
Axis	
Stainless steel AISI 304	
Axial mount	
Plastic, polyacetal (POM)	
• Operating temperature -20 °C to 90 °C	
• White	

RoHS

Accessory	Page
GN 6472.1 Lead-In Guides	QVX
GN 6472.2 End Caps	QVX
GN 6471.3 Connecting Strips	QVX
GN 6473.2 Connecting Elements	QVX

Side guides GN 6472 are installed in the middle of conveyor sections and their rollers guide the conveyed goods without damage.

The type of rollers used depends on the conveyed material. Type K is used for cans and plastic boxes. For cardboard boxes, type Z can be used for an even material flow. For containers of glass, type ZA is used since it allows easy removal of any contamination due to glass breakage.

Side guides are fastened on the top side via the T-slot. Connecting element GN 6473.2 can be used for this purpose, for example.

The side guides are delivered in packaging units of 2 pieces each. They can be shortened at increments of 120 mm in consideration of the installation situation.

see also...	Page
GN 6471 Side Guides	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

1	Type
2	Identification no.
3	Length l
4	Material
5	Color

1 2 3 4 5
GN6472-K-1-1440-AL-GR