




1 d ₁ Pin -0,05 Bore +0,1 +0,05	2 l ₂		3 d ₂	h ₁	h ₂	k	l ₁	l ₃	l ₄	l ₅	s	Spring load in N ≈	
												Initial	End
6	10	16	16	10	4,5	28	46	10	30	40	16	12	32
8	10	16	16	10	4,5	28	46	10	30	40	16	12	32
8	12	18	20	10	4,5	32	57	12	37	45	20	21	58
10	10	16	16	10	4,5	28	46	10	30	40	16	12	32
10	12	18	20	10	4,5	32	57	12	37	45	20	21	58
12	12	18	20	10	4,5	32	57	12	37	45	20	21	58

Specification

• Guide

Zinc die casting

Powder coated

Black, RAL 9005, textured finish

● SW

• Plunger

Steel

Zinc plated, blue passivated

• Lever

Plastic (Polyamide PA)

- Black, matte finish

- Not removable

• Load Rating Information → Page 2132

• Plastic Characteristics → Page 2158

• RoHS

Information

Cam action indexing plungers GN 612.10 are used in cases where the plunger must not protrude all the time. By rotating the lever through 180° the plunger withdraws itself. The groove allows safe positioning.

see also...

• List of Cam Action Indexing Plunger Types → Page 958 ff.

• Positioning Bushings GN 412.2 → Page 954

How to order	
1	d ₁
2	l ₂
3	d ₂
4	Finish