



<b>d<sub>1</sub></b>	<b>Length l</b>						<b>d<sub>2</sub></b>	<b>k</b>
M 3	6	8	10	16	20	-	12	2,5
M 4	8	10	12	16	20	25	16	3,5
M 5	10	12	16	20	25	30	20	4
M 6	12	16	20	25	30	40	24	5
M 8	16	20	25	30	35	40	30	6
M 10	20	25	30	35	40	-	36	8

Specification

- Steel
  - Property class 5
  - Visible face fine turned
  - Blackened —
  - Zinc plated, blue passivated **ZB**
- Stainless steel AISI 303 **NI**  
Matte shot-blasted
- *Strength Values of Screws* → Page 2152
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Version in stainless steel (A4 quality)

Information

Knurled screws DIN 653 are turned entirely from a single piece. The thread of the screw generally extends up to the head and ends in a runout without recess as per the DIN designation A.

They are suitable for universal use and can be quickly tightened and loosened without tools.

- see also...
- *Knurled Screws GN 653.10 (Steel, with Brass / Plastic Pivot)* → Page 650
  - *Knurled Screws GN 653.2 (with Recessed Stud for Loss Prevention)* → Page 651
  - *Knurled Screws DIN 464 (High Type)* → Page 647

How to order (Steel, blackened)		1	d <sub>1</sub>
<b>DIN 653-M8-35</b>		2	Length l

How to order (Steel, zinc plated)		1	d <sub>1</sub>
<b>DIN 653-M3-8-ZB</b>		2	Length l
		3	Finish

How to order (Stainless steel)		1	d <sub>1</sub>
<b>DIN 653-M5-20-NI</b>		2	Length l
		3	Material