



Type A




2 Type

- A Without mounting holes
- B With mounting holes

Type B



Roller track GN 646.1



Ball track GN 646.2

1

Length l											h	
											for GN 646.1 (l ₂ = 15)	for GN 646.1 (l ₂ = 27)
270	540	810	1080	1350	1620	1890	2160	2430	2700	2970	29	34

Specification

- Aluminum
Anodized, natural color
- *Load Rating Information* → Page 2008
- **RoHS**

On request

- Carrier profiles in in-between lengths (spacing 27)

Information

Carrier rail profiles GN 646.3 are the base components for roller tracks and ball tracks. They are the carrier channels for roller tracks GN 646.1 and for ball tracks GN 646.2 and feature a high degree of stiffness and rigidity.

The carrier profile is designed such that roller and ball tracks and containment edge strips GN 646.4 can be assembled without mounting hardware.

Using connectors GN 646.6 (Type C), the carrier rail profiles can be assembled together, to create longer profile extensions.

The standard lengths match the 270 length of the roller and ball tracks. For type B, the position and edge spacing of the hole pattern is not defined.

see also...

- *Roller Tracks GN 646.1* → Page 2009
- *Further Accessories for Roller Track and Ball Rail Assemblies* → Page 2012 ff.

How to order

GN646.3-810-A

- 1** Length l
- 2** Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

