



- 1) Breather caps
GN 663 / GN 774
with bayonet (BA)



- 1) Breather caps
GN 663 / GN 774 / GN 774.1
with thread



¹ d ₁	¹ d ₂	² l ₁	d ₃	d ₄	d ₅	d ₆	l ₂	l ₃	l ₄	l ₅
Thread	Bayonet									
G 1 1/4	-	94	83	56	-	49	23	9	-	-
-	BA 39	94	83	-	58	49	-	-	20	7

1) Breather caps are to be ordered separately.

Specification

- Threaded flange
Plastic
 - Glass fiber reinforced
 - Black, matte finish
- Filler strainer
Plastic
Technopolymer (Polypropylene PP)
 - Glass fiber reinforced
 - Temperature resistant up to 90 °C
 - Black, matte finish
- Flange for fitting bayonet
Steel, zinc plated, blue passivated
- Seal cork
impregnated with rubber
- *Plastic Characteristics* → Page 2158
- RoHS

On request

- Mounting flange without filler strainer

Information

Filler strainers GN 664 are available with mounting flange for threaded or bayonet (BA) connection. Filler strainers prevent the ingress of coarse impurities during the refilling process.

Six self-tapping screws are included parts of the order.

see also...

- *Filler Strainers GN 664.1 (for Side Mounting)* → Page 1636
- *Breather Caps GN 663* → Page 1612
- *Breather Caps GN 774* → Page 1620
- *Breather Caps GN 774.1* → Page 1614

How to order

GN 664-BA39-94

¹ d₂ (d₁)

² l₁



Mounting dimensions (Hole pattern)

