



4 Type

A Front rounded

1	2	3																		
b h9	h	Length l																	for shaft-Ø from to	
2	2	6	8	10	12	14	16	18	20	-	-	-	-	-	-	-	-	-	6...8	
3	3	6	8	10	12	14	16	18	20	22	25	28	30	32	35	36	-	-	8...10	
4	4	6	8	10	12	14	16	18	20	22	25	28	32	36	40	45	-	-	10...12	
5	5	8	10	12	14	16	18	20	22	25	28	32	36	40	45	50	-	-	12...17	
6	6	12	14	16	18	20	22	25	28	32	36	40	45	50	56	63	-	-	17...22	
8	7	12	14	16	18	20	22	25	28	32	36	40	45	50	56	63	70	80	22...30	
10	8	16	18	20	22	25	28	32	36	40	45	50	56	63	70	80	90	100	30...38	
12	8	20	25	28	32	36	40	45	50	56	63	70	80	90	100	125	-	-	38...44	

Specification

Steel C45

Plain

RoHS

On request

• b = 14, 16, 18, 20

Parallel keys DIN 6885 are only in packing units of 50 pieces for each size and length available.

see also...

DIN 6885 Parallel Keys

Page

QVX

Technical Information

Keyways DIN 6885-1 (High Hub Keyway)

QVX

Keyways DIN 6885-2 (Low Hub Keyway)

QVX

ISO Fundamental Tolerances

QVX

How to order

DIN 6885-6-6-28-A

- 1 b
- 2 h
- 3 Length l
- 4 Type