



elesa
Original design IEL.N / IEL.N-H SOFT



- 4 Type**
- G** Closed version
 - T** With transparent cover cap

1 d_1	2 l_1		3 d_2 Bore	l_2	d_3
	Type G	Type T			
45	47	-	B 12	-	28
45	65	65	B 10	B 12	23

Specification

Handle

- Base body
Plastic, Polypropylen (PP)
- Softline coating
Thermoplastic elastomer (TPE)
 - Chemically bonded with base body
 - FDA compliant plastic granulate
 - Operating temperature 0 °C to +80 °C
 - Black, matte finish
 - Hardness 70 Shore A

Cover cap for type T

- Plastic, Polyamide (PA-T)
- transparent
- with magnifying effect

RoHS

The softline coating makes the mushroom shaped handles GN 718.1 particularly user-friendly and ergonomic.

The soft, slip-proof contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures.

During mounting, easy blows with a soft hammer are sufficient to drive the knob into place, the shaft end should be slightly rounded or chamfered (30°). The transparent cover cap (type T) allows symbols or similar elements to be attached.

Once the mushroom shaped handle has been fitted to the shaft, the symbol is placed into the recess of the separately supplied sight glass and carefully pushed or driven into the handle.

The symbol is fully protected from dirt and liquid by the tight connection between the sight glass and the mushroom shaped handle. Positioning and control symbols are to be ordered separately.

see also...	Page
GN 518 Tapered Knobs (for Positioning Symbols)	QVX

Technical Information

Product Family Softline	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

Accessory

GN 517.1 Positioning and Control Symbols	QVX
---	-----

How to order	1 d_1
1 2 3 4	2 l_1
GN 718.1-45-65-B10-G	3 d_2
	4 Type

