


3 Type

- A** With flange for surface mounting
- B** With female thread
- C** With male thread



1 2

d	r	b	l ₁ ≈	l ₂	l ₃ min.	l ₄
17	40	10	5,5	16,5	21,5	11
17	55	10	5,5	16,5	21,5	11

Specification

- Latch
 - Zinc die casting
 - Powder coated
 - Black, RAL 9005, textured finish
 - Red, RAL 3000, textured finish
- Indexing mechanism
 - Type A
 - Zinc die casting / Plastic
 - Type B / Type C
 - Steel / Plastic
 - Steel parts zinc plated, blue passivated
- Fastening flange
 - Zinc die casting
 - Powder coated
 - Black, matte finish
- RoHS

4

Information

Stop locks GN 702 are particularly suitable for light-weight applications not exposed to dynamic loads, e.g. for keeping drawers closed.

To mount stop locks of Type C, bore holes as shown in the diagram below must be set in the attachment surface.

These mounting holes are usually made by punching or with laser. For small series and steel sheets below 2 mm thickness, the sheet metal punches GN 123 are the tool of choice → Page 1267.

The mounting bore holes can also be made by drilling / milling.

How to order

GN 702-17-40-C-SW

- 1** d
- 2** r
- 3** Type
- 4** Color